



SPA001N

### Cartridge N-PE Uc 350V Iimp 100kA Up 1.5kV

#### Technical characteristics

##### Main electrical features

Frequency	50/60 Hz
-----------	----------

##### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	100 kA
-------------------------------------	--------

##### Dimensions

Depth of installed product	52.3 mm
Height of installed product	46.4 mm
Width of installed product	35.5 mm

##### Standards

European directive WEEE	concerned
-------------------------	-----------

##### Safety

Protection index IP	IP20
---------------------	------

##### Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------