



WRCC50NPSW



## 45A Cooker Control Unit Polished Steel White Insert

### Technical characteristics

#### Electric current

Rated current 45 A

#### Voltage

Rated voltage 250 V

#### Connection

Conductor cross-section 16 - 16 mm<sup>2</sup>

#### Safety

Ingress Protection (IP) class IP20

#### Dimensions

Height 86 mm

Width 146 mm

Depth 39.60 mm

#### Materials

Colour Silver

Surface finish Glossy

Material Stainless steel

#### Installation, mounting

Mounting on Flush mounting

#### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

#### Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp Yes

#### Accessories

Has labelling field No

#### Capacity

Number of modules 0

**Texts**

---

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads

---