



WRCC50NPSW



45A Cooker Control Unit Polished Steel White Insert

Technical characteristics

Electric current

Rated current	45 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Connection

Conductor cross-section	16 - 16 mm ²
-------------------------	-------------------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Height	86 mm
Width	146 mm
Depth	39.60 mm

Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	Yes

Accessories

Has labelling field	No
---------------------	----

Capacity

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads