



SPB015

Cartridge T2 L-N Uc 275V I_{max} 40kA Up 1.35kV

Technical characteristics

Controls and indicators

Indicator lamp	Optic
----------------	-------

Main electrical features

Rated operational voltage U _e	240 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	43.3 mm
Height of installed product	52.4 mm
Width of installed product	17.5 mm

Installation, mounting

Tightening torque	3
-------------------	---

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------