



SPB015N

Cartridge T2 N-PE Uc 260V I_{max} 40kA Up 1.5kV

Technical characteristics

Main electrical features

Rated operational voltage U _e	240 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	43.3 mm
Height of installed product	52.4 mm
Width of installed product	17.5 mm

Installation, mounting

Tightening torque	3
-------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------