



SPB015N

**Cartridge T2 N-PE Uc 260V I<sub>max</sub> 40kA Up 1.5kV**

**Technical characteristics**

**Controls and indicators**

|                |       |
|----------------|-------|
| Indicator lamp | Optic |
|----------------|-------|

**Main electrical features**

|  |          |
|--|----------|
| Rated operational voltage U <sub>e</sub> | 240 V    |
| Frequency                                | 50/60 Hz |

**Dimensions**

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 43.3 mm |
| Height of installed product | 52.4 mm |
| Width of installed product  | 17.5 mm |

**Installation, mounting**

|                   |   |
|-------------------|---|
| Tightening torque | 3 |
|-------------------|---|

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -40...80 °C |
|-----------------------|-------------|