
:hager



Meter Box Switch
Notice d'instructions
User instructions
Bedienungsanleitung
Instrucciones de uso
Instruções
Bruksanvisning
Gebruiksaanwijzing



Scan with your smartphone
QR scanner to be taken
straight to the Meter Box
Switch features video, or visit
hager.co.uk/youtube


Complies with BS EN 60947-3 which facilitates the installation to comply with BS7671 IET wiring regulations in particular the guidance in table 53.4.

Rated insulation voltage (U_i) 300V Rated impulse voltage (U_{imp}) 6kV Polution degree: 2


Rated duty: uninterrupted duty


Rated short-time withstand current: 1500 A/1s Rated short-circuit making capacity: 2115A Rated conditional short-circuit (I_{cc})* 16kA Type of conductors: Rigid 16/25/35mm²


*Short-circuit protective device: 100A BS 88-3 Fuse. (Fuses mainly for household or similar applications)



Strip/dress cables, 16/25/35mm² can be used (17mm strip length required)












x 6 ZB0217



x 1 ZM0248 (3 parts)




x 1 ZM0245



x 1 ZM0247



x 1 ZM0246



x 1 SBR290 (100A)

