



SPN080N

Cartridge neutral 25kA class 1 for SPN802 and SPN802R

Technical characteristics

Controls and indicators

Indicator lamp yes

Main electrical features

Frequency 50/60 Hz

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 25 kA

Power

Total power loss under I_N 0 W

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -40...60 °C