



SPN080N

### Cartridge neutral 25kA class 1 for SPN802 and SPN802R

#### Technical characteristics

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Max discharge (I<sub>max</sub>) L-N(PEN)/ N-PE 25 kA

#### Power

Total power loss under I<sub>N</sub> 0 W

#### Use conditions

Operating temperature -40...60 °C