



TXA112

IP20

Power supply 30V DC 640 mA

Technical characteristics

Architecture

Bus system EIB

Main electrical features

Frequency 50/60 Hz

Fuse

Fuse with electronic short-circuit and overload protection

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Width of installed product 72 mm

Power

Total power loss under IN 15 W

Materials

RAL colour RAL 7035 - Light grey

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of connection quick connect

Type of connection with QuickConnect plug-in terminals

Use conditions

Operating temperature -5...45 °C