

Consumer Unit Design 30 Dual Row Split Load


For the distribution of power in a residential application, conforming to BS EN 61439-3 including Annex ZB (16kA rating).

Design 30 dual row is the enhanced board for use in applications where the consumer unit is located in a living area of the dwelling.

The board is designed to allow compliance with BS 7671:2008 regulations; 411.3.3 additional protection by means of a 30mA RCD, 314.1&2 segregation of circuits to avoid danger and minimise inconvenience in the event of a fault, 522.6.202 protection of wiring concealed in walls or partitions.

Metal enclosure manufactured to allow compliance with BS 7671 regulation 421.1.201

A split load board allows circuits to be arranged in a configuration to minimise inconvenience to the householder in case of an earth leakage fault.



VM71214H

Description	Size	Cat ref.	Cat ref. With Knockouts
4+6 Way 100A Switch 2x63A 30mA RCCB Dual Row	3 (2)	VM746H	VM746HK
8+10 Way 100A Switch 2x63A 30mA RCCB Dual Row	4 (2)	VM70810H	VM70810HK
12+14 Way 100A Switch 2x63A 30mA RCCB Dual Row	5 (2)	VM71214H	VM71214HK
18+20 Way 100A Switch 2x63A 30mA RCCB Dual Row	7 (2)	VM71820H	VM71820HK
4+6 Way 100A Switch 2x80A 30mA RCCB Dual Row	3 (2)	VM846H	VM846HK
8+10 Way 100A Switch 2x80A 30mA RCCB Dual Row	4 (2)	VM80810H	VM80810HK
12+14 Way 100A Switch 2x80A 30mA RCCB Dual Row	5 (2)	VM81214H	VM81214HK
18+20W 100A Switch 2x80A 30mA RCCB Dual Row	7 (2)	VM81820H	VM81820HK

Devices

MCB 6kA 6A to 63A B Curve

MTN***

Features & Benefits

- Provides for large quantities of outgoing ways or space for additional devices
- Enclosure fully open between rows giving easy access for cables
- Square cable entry points top and bottom for use with cable trunking
- Meter tail cable entry plate (VM04CE) provided
- Rigid top wall – Enhances rigidity to prevent distortion when removing knockouts
- Rear Knockouts for ease of cable entry – Cable protector plate (VM02CE) provided
- Front cover retained screws – Prevents loss during installation
- Full metal DIN rail – Secure and stable attachment of devices
- Quick release clip on RCBO – Allows removal of RCBO with busbar still in place
- Optimised cabling space – DIN rail position allows maximum cabling space
- Top mounted terminal rail for each row makes the wiring of the neutral and earth connections neat and simple.
- Torque settings displayed inside front cover – easily accessible to electrician during installation and maintenance.

Technical Characteristics

Standards	BS EN 61439-3
Classification	Consumer Unit
Rated & Operational Voltage (U_n/U_e)	230V a.c 50 Hz
Rated Insulation Voltage (U_i)	320V a.c. 50Hz
Rated Frequency (fn)	50 Hz
Rated impulse withstand voltage (U_{imp})	4kV
Rated Current of the Assembly (I_{na})	100A
Rated Current of an Outgoing Circuit I_{nC}	MCB 6A - 63A (Marked Rated Current on Device)
Rated Conditional Short Circuit of the Assembly (I_{cc})	Annex ZB: 16kA rms at 250V, power factor 0.6 with equipment and arrangements specified in Hager's technical documentation/catalogue
Rated Current of outgoing unit (I_{nC})	RCCB 63A - 80A (marked rated current on device)
Protection against electric shock	Consumer Unit shall be installed in an electrical system conforming to IEC 60364 / BS 7671
Rated Diversity Factor (RDF) / Values of assumed loading	10 way and above - 0.5
<p>Note: RDF only applies to continuously and simultaneously loaded circuits. In principle, this means adjacent circuit breakers having a load on time exceeding 30 minutes or where a load not exceeding 30 minutes has an 'off' time less than the 'on' time will need to have the rated diversity factor applied as indicated.</p>	
Pollution Degree	2
Types of System Earthing for which the assembly is designed	TNC-S and TN-S when installed in an electrical system conforming to BS 7671
Intended locations	Indoor use only
Stationary assembly	
Degree of protection	IP2XC with door open / closed and full compliment of devices / blanks fitted. Note: Where cables are installed through the top wall of the enclosure, gaps of IP4X to be maintained.
Intended use	Intended for use in domestic (residential) or similar premises
Electromagnetic compatibility (EMC) classification	EMC environment B
External design	Wall mounted, surface type, enclosed assembly.
Mechanical impact protection	IK05
Type of construction	Fixed parts
Incoming Line/Neutral terminal	50mm ²
Incoming Earth Terminal	16mm ²

Warranty - Hager undertakes to replace or repair at its discretion products should they become inoperable within the time periods as stated - 2 Years

Accessories

Top Wall cable entry plates	Provide more options for cable entry, when used with 50x50mm trunking IP ratings can be achieved.	VM03CE
Blind cable entry plates	A blank plate for drilling which allows the installer to decide on the method of incoming cables - compression gland etc.	VM04CB, VM03CB
Health and safety lock and padlock	Provides the ability to lock the consumer unit during the installation process	VMHBL, JK25A
Design 30 door locking kit	Allows the board to be lockable	VMLOCK
Grommet strip	For protecting cables against damage when entering the board	VM05GS
Rear stand off plates	To stand consumer unit off wall allowing surface mounted cables to enter through rear of unit.	VM01SP

Dual Row Design 30 Dimensions (mm)

	Enclosure Size				
	3 (2)	4 (2)	5 (2)	6 (2)	7 (2)
Height	480	480	480	480	480
Width	221	293	364	400	472
Depth	102.5	102.5	102.5	102.5	102.5

	Number of Knockouts				
<input type="checkbox"/> Top Face 30 x 25 (mm)	2	2	2	2	2
<input type="checkbox"/> Top Face 40 x 30 (mm)	2	4	4	6	6
<input type="checkbox"/> Back 100 x 50 (mm)	2	2	6	6	6
<input type="checkbox"/> Bottom Face 30 x 25 (mm)	3	4	4	5	5

