



TXA112



Power supply 30V DC 640 mA

Technical characteristics

Architecture

Fixing mode Din-Rail

Main electrical features

Frequency 50/60 Hz

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Width of installed product 72 mm

Power

Total power loss under IN 15 W

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C