



TXA664AN



## DIMMER 4 CHANNELS 300W NE WITH PARALLELIZATION

### Technical characteristics

#### Architecture

Fixing mode REG

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Main electrical features

Frequency 50/60 Hz

#### Fuse

Fuse short-circuit and overload proof (electronic fuse),  
overheating protection (display using LEDs)

#### Power

Incandescent bulb power 5 / 300 W

Total power loss under IN 0.35 W

Power dissipation per coil 1 W

#### Power supply

Supply voltage 230 V +10% / -15%

#### Materials

Colour light grey

#### Incandescent bulbs control

Max. power with incandescent lamps 300 W

#### Connection

Type of load universal

#### Equipment

Dimming principle phase cut-on or cut-off according to load type, self-learning

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -5...45 °C