


TXA664AN



**IP20**

## DIMMER 4 CHANNELS 300W NE WITH PARALLELIZATION

### Technical characteristics

#### Architecture

Bus system yes

#### Functions

Function Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Main electrical features

Frequency 50/60 Hz

#### Fuse

Fuse short-circuit and overload proof (electronic fuse) ; short-circuit proof and overload proof (display using LEDs) ; overheating protection (display using LEDs)

#### Power

Incandescent bulb power 5 / 300 W

Total power loss under IN 0.35 W

Power dissipation per coil 1 W

#### Power supply

Supply voltage 230 V +10% / -15%

#### Materials

Colour light grey

#### Incandescent bulbs control

Max. power with incandescent lamps 300 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2,5mm<sup>2</sup>

Type of load universal

Type of connection quick connect

Type of connection with QuickConnect plug-in terminals

#### Equipment

Subject to technical modifications

---

Dimming principle

phase cut-on or cut-off according to load type, self-learning ; minimum/maximum dimming values per channel settable on device

**Safety**

---

Protection index IP

IP20

Protection

with overheating, overload and short-circuit protection

**Use conditions**

---

Operating temperature

-5...45 °C