



VM118SPD

Design 30, 18 way 100A SW SPD

Technical characteristics

Installation, mounting

| | |
|----------------------------|------------------|
| Mounting on | Surface mounting |
| Suitable for outdoor usage | No |

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection | No |

Capacity

| | |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Dimensions

| | |
|-----------------------|-----------|
| Depth | 102.50 mm |
| Height | 240 mm |
| Width | 472 mm |
| Thickness of sidewall | 1 mm |

Cover, door

| | |
|---------------------------|----|
| Interlockable | No |
| Door/cover is transparent | No |

Materials

| | |
|----------|------------|
| RAL code | 9010 |
| Colour | Pure white |
| Material | Steel |

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 1 |
|-----------------------------|---|

Scope of delivery

| | |
|-----------------------------|---|
| Number of RCCB in enclosure | 0 |
|-----------------------------|---|

Equipment

| | |
|-----------------|---|
| Number of rows | 1 |
| Number of rails | 1 |

| | |
|--------------------|----|
| Extension possible | No |
|--------------------|----|

Safety

| | |
|-------------------------------|-------|
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP2XC |