



VMA90910H

**Dual Row 100A Sw, 2\*100A 30mA RCCB, 9+10 Way, 2 pole busbar, ARC Fault**

**Technical characteristics**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Main electrical features**

Frequency	50 Hz
-----------	-------

**Dimensions**

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	472 mm

**Cover, door**

Interlockable	No
---------------	----

**Materials**

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

**Equipment**

Number of rows	2
Can be accessorized	Yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection class	isol.class II
------------------	---------------