



VML61014CUSPD

Dual Row,10+14 Way 63A Switch 2*63A Type A RCCB Type 2 SPD

Technical Characteristics

Fixing mode	surface-mounting
Rated current	63 A
Depth of installed product	100 mm
Height of installed product	486 mm
Width of installed product	370 mm
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC