



VML612CU

12 Way Hi Integrity Configurable 63A Switch 2*63A 30mA Type A RCCB

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	83 mm
Height of installed product	246 mm
Width of installed product	406 mm

Cover, door

Interlockable	No
---------------	----

Equipment

Number of rows	1
Can be accessorized	Yes