



VML712TG

Consumer unit, Design 10, 12 way, config, 100A, 100mA, time delayed, RCCB+ 63A, 30mA, RCCB

Technical Characteristics

Fixing mode	surface-mounting
Rated current	100 A
Depth of installed product	98.2 mm
Height of installed product	245 mm
Width of installed product	368.4 mm
Number of modules	12
Type of door closing	non keylock
Interlockable	No
RAL colour number	9010
Material	Steel
Number of rows	1
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP2XC
