



VML90810H

Dual Row 8+10W 100A Switch 2*100A 30mA RCCB

Technical Characteristics

Fixing mode	surface-mounting
Rated current	100 A
Depth of installed product	100 mm
Height of installed product	485 mm
Width of installed product	296.8 mm
Number of modules	18
Type of door closing	non keylock
Interlockable	No
RAL colour number	9010
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC