



VML91014CUSPD

**Dual Row,10+14 Way Hi Integrity 100A Switch 2\*100A 30mA Type RCCB Type 2 SPD**

**Technical characteristics**

**Architecture**

Fixing mode surface-mounting

**Dimensions**

Depth of installed product 100 mm

Height of installed product 486 mm

Width of installed product 370 mm

**Cover, door**

Interlockable No

**Materials**

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

**Equipment**

Number of rows 2

Can be accessorized Yes

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP2XC