



VML91014CUSPD

Dual Row,10+14 Way Hi Integrity 100A Switch 2*100A 30mA Type RCCB Type 2 SPD

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	100 mm
Height of installed product	486 mm
Width of installed product	370 mm

Cover, door

Interlockable	No
---------------	----

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Equipment

Number of rows	2
Can be accessorized	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------