



VML91214H

Dual Row 12+14W 100A Switch 2*100A 30mA RCCB

Technical characteristics

Architecture

Fixing mode surface-mounting

Dimensions

Depth of installed product 100 mm

Height of installed product 485 mm

Width of installed product 368.4 mm

Cover, door

Type of door closing non keylock

Interlockable No

Materials

Material Steel

Equipment

Number of rows 2

Can be accessorized Yes

Standards

European directive WEEE concerned

Safety

Protection index IP IP2XC