



VML91620CUSPD

Design 10, Dual Row, 16+20 Way HI 100A Sw 2*100A 30mA RCCB Type A SPD

Technical characteristics

Architecture

Fixing mode surface-mounting

Dimensions

Depth of installed product 100 mm

Height of installed product 486 mm

Width of installed product 478 mm

Cover, door

Interlockable No

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Equipment

Number of rows 2

Can be accessorized Yes

Standards

European directive WEEE concerned

Safety

Protection index IP IP2XC