



WFCC50NPSW



## 45A Cooker Control Unit Polished Steel White Insert

### Technical characteristics

#### Electric current

Rated current	45 A
---------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Connection

Conductor cross-section	16 - 16 mm <sup>2</sup>
-------------------------	-------------------------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Dimensions

Height	86 mm
--------	-------

Width	146 mm
-------	--------

Depth	39.60 mm
-------	----------

#### Materials

Colour	Silver
--------	--------

Surface finish	Glossy
----------------	--------

Material	Stainless steel
----------	-----------------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

#### Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	Yes
------------------	-----

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	0
-------------------	---

**Texts**

---

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads

---