



WMGKS



20A Double Pole Key Switch

Technical characteristics

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Number of poles	2
-----------------	---

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
With feedback signal contact	No

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Transparent	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Dimensions

Depth	24 mm
-------	-------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Imprint	Without imprint
Lighting	Without neon lamp
Related Systems	Hager sollysta