

Hager sollysta





## 20A Double Pole Key Switch Marked 'EM LTG TEST'

## **Technical characteristics**

Voltage	
Rated voltage	250 V
Architecture	
Number of poles	2
Installation, mounting	
Mounting on	Flush mounting
Controls and indicators	
Number of buttons	0
With feedback signal contact	No
Materials	
Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Transparent	No
Connectivity	
Type of connection	Screw terminal
Dimensions	
Depth	24 mm
Safety	
Ingress Protection (IP) class	IP20
Texts	
Imprint	With imprint
Lighting	Without neon lamp

Related Systems