



WMSS82

2 Gang Double Pole Switched Socket Dual Earth

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

Dimensions

Depth	29.5 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	white
Type of surface treatment	untreated

Connection

Type of connection	screw
--------------------	-------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection