



WMSS82-USBAC

## Double Pole Switched Socket 2 Gang Complete With Twin USB A+C Ports

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Rated voltage 220...240 V AC

#### Dimensions

Depth 19 mm

Height 86 mm

Width 146 mm

#### Cover, door

Cover Full cover plate

#### Materials

Colour white

Material Urea-formaldehyde

Surface appearance glossy

Type of surface treatment untreated

#### Connection

Type of connection screw

#### Cable

Wiring with double earth connection

#### Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

#### Safety

Protection index IP IP20

Protection Enhanced contact protection