



WRCC50NPSW

### 45A Cooker Control Unit Polished Steel White Insert

#### Technical characteristics

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	45 A

##### Dimensions

Depth	39.6 mm
Height	86 mm
Width	146 mm

##### Cover, door

Cover	Full cover plate
-------	------------------

##### Materials

Surface appearance	glossy
Type of surface treatment	Other

##### Connection

Type of connection	Screw connection
--------------------	------------------

##### Cable

Wiring	with double earth connection
--------	------------------------------

##### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

##### Safety

Protection	to protect downstream loads
------------	-----------------------------

##### Use conditions

Insert	insert white
--------	--------------